

# Mains Cable



nVent SCHROFF Mains cable provides practical, universal fastening with variable attachment facilities. They are general in nature and fit in to different applications like Fans, cabinet lights, etc., Industrial PC connections, Uninterruptible power supplies, Systems.

## CERTIFICATIONS



## CARACTERISTICI

Applications: Fans, cabinet lights, Industrial PC connections, Uninterruptible power supplies and Systems

## SPECIFICAȚII

**Product Type:** Cable

Table 1/2

| Număr de catalog | Input Connector       | Output Connector | Length | Package Quantity | Color | Connector Type |
|------------------|-----------------------|------------------|--------|------------------|-------|----------------|
| 62150-191        | SCHUKO / UTE          | IEC C13          | 2500mm | 1                | Black | Straight       |
| 60704-020        | SCHUKO / UTE          | IEC C13          | 2500mm | 1                | Grey  | Angled         |
| 60103-131        | SCHUKO / UTE          | IEC C13          | 2500mm | 1                | Grey  | Straight       |
| 60110-361        | IEC C14               | IEC C13          | 1000mm | 1                | Black | Straight       |
| 60197-053        | IEC C14               | IEC C13          | 2500mm | 1                | Black | Straight       |
| 60110-360        | IEC C14               | IEC C13          | 500mm  | 1                | Black | Straight       |
| 60103-137        | BS = British Standard | IEC C13          | 2500mm | 1                | Black | Straight       |

| Număr de catalog | InputConnector   | Output Connector | Length | Package Quantity | Color | ConnectorType |
|------------------|------------------|------------------|--------|------------------|-------|---------------|
| 60103-141        | US = US Standard | IEC C13          | 2500mm | 1                | Black | Straight      |

Table 2/2

| Număr de catalog | Material |
|------------------|----------|
| 62150-191        | PVC      |
| 60704-020        | PVC      |
| 60103-131        | PVC      |
| 60110-361        | PVC      |
| 60197-053        | PVC      |
| 60110-360        | PVC      |
| 60103-137        | PVC      |
| 60103-141        | PVC      |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**