

PropacPRO Case Design Elements

To individualize the PropacPRO case design. The elements will be screwed from the rear side of the die cast frame.



CERTIFICATIONS



CARACTERISTICI

To individualize the case design

Available in 3 forms and two colors

SPECIFICAȚII

Material:	Aluminiu
Finish:	Anodized
Works With:	Cases
Product Type:	Corner Profile
Product Family:	PropacPRO

Table 1/1

Număr de catalog	Rack Width	Type	Color Code	Color
20850-299	42HP	Rounded	RAL 5007	Brilliant Blue
20850-196	42HP	Triangle	RAL 7035	Light Grey
20850-190	42HP	Squared	RAL 7035	Light Grey
20850-315	42HP	Squared	RAL 5007	Brilliant Blue

Număr de catalog	Rack Width	Type	Color Code	Color
20850-184	42HP	Rounded	RAL 7035	Light Grey
20850-331	42HP	Triangle	RAL 5007	Brilliant Blue
20850-185	63HP	Rounded	RAL 7035	Light Grey
20850-191	63HP	Squared	RAL 7035	Light Grey
20850-197	63HP	Triangle	RAL 7035	Light Grey
20850-316	63HP	Squared	RAL 5007	Brilliant Blue
20850-332	63HP	Triangle	RAL 5007	Brilliant Blue
20850-300	63HP	Rounded	RAL 5007	Brilliant Blue
20850-192	84HP	Squared	RAL 7035	Light Grey
20850-198	84HP	Triangle	RAL 7035	Light Grey
20850-186	84HP	Rounded	RAL 7035	Light Grey
20850-317	84HP	Squared	RAL 5007	Brilliant Blue
20850-333	84HP	Triangle	RAL 5007	Brilliant Blue
20850-301	84HP	Rounded	RAL 5007	Brilliant Blue

DETALII SUPLIMENTARE DESPRE PRODUS

Size 28 HP and further colors available on request.

Cannot be combined with front hood.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE