






TOOLS


CABLE STRIPPING TOOLS

Product name	Order reference	Description
Sheathmaster 	GL	Hand-type stripping tool to strip the sheath of copper-sheathed MI cable. For use with MI cable sizes up to and including 250 kcmil.
	GLB	Replacement blade for Sheathmaster GL tool.
Ratchet stripper kit 	RSTRIPKIT	Ratchet sheath stripper head for stripping the sheath of copper-sheathed MI cables with diameters of 0.684 inches and greater. The ratchet stripper head must be inserted into a conduit threading tool such as the RIDGID® Model 00-R (included), or RIDGID® Model 770 power driver tool with 00-R adapter or equivalent (not included).
	PSTRIPB	A cable guide bushing (not included) is required for each cable diameter to be stripped (see below). Replacement blade for ratchet stripper head.
Cable guide bushing 	PSBUSH1000	Bushing for 1" diameter cable
	PSBUSH975	Bushing for 0.975" diameter cable
	PSBUSH865	Bushing for 0.865" diameter cable
	PSBUSH834	Bushing for 0.834" diameter cable
	PSBUSH768	Bushing for 0.768" diameter cable
	PSBUSH746	Bushing for 0.746" diameter cable
	PSBUSH730	Bushing for 0.730" diameter cable
	PSBUSH710	Bushing for 0.710" diameter cable
PSBUSH684	Bushing for 0.684" diameter cable	





PYROPOTTER, CRIMPING AND COMPRESSION TOOLS

Product name	Order reference	Description
Pyropotter pot threading tool 	PYROPOT12	The Pyropotter tool simplifies installation of the pot, allowing it to be installed more quickly, accurately and securely than by any other means.
	PYROPOT34	Tool to install 1/2 in pot
	PYROPOT1	Tool to install 3/4 in pot
	PYROPOT114	Tool to install 1 in pot
		Tool to install 1-1/4 in pot
Handle type crimping and compression tool 	MIC1/2	Heavy duty handle type crimping and compression tool easily completes the MI cable termination. For use with termination kits using fiber caps and mastic compound seal.
	MIC3/4	1/2" crimping and compression tool 3/4" crimping and compression tool



PYROPOTTER, CRIMPING AND COMPRESSION TOOLS

Product name	Order reference	Description
		Screw type crimping and compression tool easily completes the MI cable termination. For use with termination and splice kits using fiber caps and mastic compound seal.
	CC1/2	1/2" crimping and compression tool
	CC3/4	3/4" crimping and compression tool
	CC1	1" crimping and compression tool
	CC11/4	1-1/4" crimping and compression tool for cable diameters from 0.699" to 0.84"
	CC11/4M	1-1/4" crimping and compression tool for cable diameters from 0.84" to 1.00"


CABLE HANDLING TOOLS

Product name	Order reference	Description
	HANDVISE	Vise-grip-type tool used to support cable while installing termination.
		Bending tool assists in making bends in MI cable.
	HICMED	Medium size 0.39" – 0.63" OD cable
	HICLGE	Large size 0.63" – 0.75" OD cable
	HIC114	Extra large size 0.75" – 1.25" OD cable
		Heavy duty bending tool specially modified to prevent damage to the MI cable sheath when making bends in the cable. Fits a standard conduit bending tool handle with 1" threads (handle not supplied).
	PYROHICKEY381	Bends 3/8" to 1" MI cable
	STRSM	Manual tool to straighten MI cables up to 1/2" in diameter.

BANDING TOOLS

Product name	Order reference	Description
	T34P	Ratchet-type tensioning tool tightens stainless-steel banding used to support MI cables.
	S12P	Crimping tool used to crimp clip onto stainless steel banding.

TWISTED PAIR DRAIN WIRE TOOL

Product name	Order reference	Description
	TWISTPRTOOL	Drain wire tool used to fix drain wire ring to shield of shielded twisted-pair copper-sheathed MI cable.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com



[nVent.com/PYROTENAX](https://www.nvent.com/PYROTENAX)

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER