

Panhead Screw, Torx

Panhead screws.



CERTIFICATIONS



CARACTERISTICI

Panhead screw

SPECIFICAȚII

Type: Panhead Screw
Product Type: Screw
Material: Oțel

Table 1/2

Număr de catalog	Length	Finish	Package Quantity	Thread Size	Product Family	Works With
24560-148	10mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-147	7mm	Nickel Plated	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP

Număr de catalog	Length	Finish	Package Quantity	Thread Size	Product Family	Works With
24560-161	12mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-135	6mm	Oțel Zincat	100	M4	EuropacPRO	Subracks
24571-372	10mm	Oțel Zincat	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
24571-371	14mm	Oțel Zincat	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
24560-178	6mm	Nickel Plated	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
24560-162	14mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-163	16mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters

Table 2/2

Număr de catalog	Torque
24560-148	0.3N·m
24560-147	0.3N·m
24560-161	0.3N·m
24560-135	1.3N·m
24571-372	2.4N·m
24571-371	2.4N·m
24560-178	
24560-162	
24560-163	

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE