

# Varistar CP ,

## Data Solutions

?? Varistar CP ??????????



??

????, ??????????

?????????

????

 :  /

Table 1/5

						
21630-049	52U	2450mm	1000mm	IP20	2	
21630-270	33U	1600mm	800mm	IP20	2	
21630-050	52U	2450mm	1100mm	IP20	2	
21630-279	42U	2000mm	800mm	IP20	2	
21630-280	42U	2000mm	900mm	IP20	2	
21630-269	33U	1600mm	600mm	IP20	2	
21630-234	38U	1800mm	800mm	IP55	2	
21630-080	47U	2200mm	1000mm	IP55	2	
21630-268	29U	1400mm	1000mm	IP20	2	
21630-479	47U	2200mm	800mm	IP55	2	
21630-226	29U	1400mm	800mm	IP55	2	
21630-235	38U	1800mm	900mm	IP55	2	

Part Number	Units	Width (mm)	Depth (mm)	IP Rating	Quantity	Notes
21630-471	38U	1800mm	600mm	IP55	2	
21630-478	47U	2200mm	600mm	IP55	2	
21630-267	29U	1400mm	900mm	IP20	2	
21630-281	47U	2200mm	300mm	IP20	2	
21630-236	38U	1800mm	1000mm	IP55	2	
21630-480	47U	2200mm	900mm	IP55	2	
21630-266	29U	1400mm	800mm	IP20	2	
21630-225	29U	1400mm	600mm	IP55	2	

Table 2/5

Part Number	Units	Width (mm)	Depth (mm)	IP Rating	Quantity	Notes
21630-265	29U	1400mm	600mm	IP20	2	
21630-927	24U	1200mm	900mm	IP55	2	
21630-048	47U	2200mm	1200mm	IP20	2	
21630-237	42U	2000mm	300mm	IP55	2	
21630-470	33U	1600mm	800mm	IP55	2	
21630-081	47U	2200mm	1100mm	IP55	2	
21630-476	42U	2000mm	900mm	IP55	2	
21630-229	33U	1600mm	600mm	IP55	2	
21630-276	38U	1800mm	1000mm	IP20	2	
21630-275	38U	1800mm	900mm	IP20	2	
21630-078	42U	2000mm	1100mm	IP55	2	
21630-475	42U	2000mm	800mm	IP55	2	
21630-230	33U	1600mm	800mm	IP55	2	
21630-474	42U	2000mm	600mm	IP55	2	
21630-077	42U	2000mm	1000mm	IP55	2	
21630-277	42U	2000mm	300mm	IP20	2	
21630-274	38U	1800mm	800mm	IP20	2	
21630-473	42U	2000mm	300mm	IP55	2	
21630-228	29U	1400mm	1000mm	IP55	2	
21630-264	24U	1200mm	1000mm	IP20	2	

Table 3/5

Part Number	Units	Width (mm)	Depth (mm)	IP Rating	Quantity	Notes
21630-231	33U	1600mm	900mm	IP55	2	

Part Number	Height	Width	Depth	IP Rating	Quantity	Notes
21630-273	38U	1800mm	600mm	IP20	2	
21630-079	42U	2000mm	1200mm	IP55	2	
21630-272	33U	1600mm	1000mm	IP20	2	
21630-051	52U	2450mm	1200mm	IP20	2	
21630-477	47U	2200mm	300mm	IP55	2	
21630-278	42U	2000mm	600mm	IP20	2	
21630-232	33U	1600mm	1000mm	IP55	2	
21630-472	38U	1800mm	800mm	IP55	2	
21630-271	33U	1600mm	900mm	IP20	2	
21630-227	29U	1400mm	900mm	IP55	2	
21630-233	38U	1800mm	600mm	IP55	2	
21630-247	47U	2200mm	900mm	IP55	2	
21630-284	47U	2200mm	900mm	IP20	2	
21630-223	24U	1200mm	900mm	IP55	2	
21630-082	47U	2200mm	1200mm	IP55	2	
21630-241	42U	2000mm	1000mm	IP55	2	
21630-045	42U	2000mm	1200mm	IP20	2	
21630-249	47U	2200mm	1100mm	IP55	2	
21630-468	29U	1400mm	800mm	IP55	2	

Table 4/5

Part Number	Height	Width	Depth	IP Rating	Quantity	Notes
21630-248	47U	2200mm	1000mm	IP55	2	
21630-465	24U	1200mm	600mm	IP55	2	
21630-932	33U	1600mm	1000mm	IP55	2	
21630-242	42U	2000mm	1100mm	IP55	2	
21630-044	42U	2000mm	1100mm	IP20	2	
21630-931	33U	1600mm	900mm	IP55	2	
21630-222	24U	1200mm	800mm	IP55	2	
21630-933	38U	1800mm	900mm	IP55	2	
21630-243	42U	2000mm	1200mm	IP55	2	
21630-221	24U	1200mm	600mm	IP55	2	
21630-246	47U	2200mm	800mm	IP55	2	
21630-467	29U	1400mm	600mm	IP55	2	
21630-934	38U	1800mm	1000mm	IP55	2	

Item No.	Height	Width	Depth	IP Rating	Qty	Notes
21630-043	42U	2000mm	1000mm	IP20	2	
21630-466	24U	1200mm	800mm	IP55	2	
21630-245	47U	2200mm	600mm	IP55	2	
21630-244	47U	2200mm	300mm	IP55	2	
21630-928	24U	1200mm	1000mm	IP55	2	
21630-469	33U	1600mm	600mm	IP55	2	
21630-262	24U	1200mm	800mm	IP20	2	

Table 5/5

Item No.	Height	Width	Depth	IP Rating	Qty	Notes
21630-250	47U	2200mm	1200mm	IP55	2	
21630-929	29U	1400mm	900mm	IP55	2	
21630-239	42U	2000mm	800mm	IP55	2	
21630-224	24U	1200mm	1000mm	IP55	2	
21630-283	47U	2200mm	800mm	IP20	2	
21630-263	24U	1200mm	900mm	IP20	2	
21630-261	24U	1200mm	600mm	IP20	2	
21630-047	47U	2200mm	1100mm	IP20	2	
21630-282	47U	2200mm	600mm	IP20	2	
21630-046	47U	2200mm	1000mm	IP20	2	
21630-930	29U	1400mm	1000mm	IP55	2	
21630-238	42U	2000mm	600mm	IP55	2	
21630-240	42U	2000mm	900mm	IP55	2	

Table 1/5

Item No.	Color	Width	Depth	Notes
21630-049	RAL 7021	2000mm	600mm	
21630-270	RAL 7021	2000mm	600mm	
21630-050	RAL 7021	2000mm	600mm	
21630-279	RAL 7021	2000mm	600mm	
21630-280	RAL 7021	2000mm	600mm	
21630-269	RAL 7021	2000mm	600mm	
21630-234	RAL 7021	2000mm	600mm	
21630-080	RAL 7021	2000mm	600mm	
21630-268	RAL 7021	2000mm	600mm	

Item	Color	Material	Finish	Notes
21630-479	RAL 7021	Steel	Paint	Standard
21630-226	RAL 7021	Steel	Paint	Standard
21630-235	RAL 7021	Steel	Paint	Standard
21630-471	RAL 7021	Steel	Paint	Standard
21630-478	RAL 7021	Steel	Paint	Standard
21630-267	RAL 7021	Steel	Paint	Standard
21630-281	RAL 7021	Steel	Paint	Standard
21630-236	RAL 7021	Steel	Paint	Standard
21630-480	RAL 7021	Steel	Paint	Standard
21630-266	RAL 7021	Steel	Paint	Standard
21630-225	RAL 7021	Steel	Paint	Standard

Table 2/5

Item	Color	Material	Finish	Notes
21630-265	RAL 7021	Steel	Paint	Standard
21630-927	RAL 7021	Steel	Paint	Standard
21630-048	RAL 7021	Steel	Paint	Standard
21630-237	RAL 7021	Steel	Paint	Standard
21630-470	RAL 7021	Steel	Paint	Standard
21630-081	RAL 7021	Steel	Paint	Standard
21630-476	RAL 7021	Steel	Paint	Standard
21630-229	RAL 7021	Steel	Paint	Standard
21630-276	RAL 7021	Steel	Paint	Standard
21630-275	RAL 7021	Steel	Paint	Standard
21630-078	RAL 7021	Steel	Paint	Standard
21630-475	RAL 7021	Steel	Paint	Standard
21630-230	RAL 7021	Steel	Paint	Standard
21630-474	RAL 7021	Steel	Paint	Standard
21630-077	RAL 7021	Steel	Paint	Standard
21630-277	RAL 7021	Steel	Paint	Standard
21630-274	RAL 7021	Steel	Paint	Standard
21630-473	RAL 7021	Steel	Paint	Standard
21630-228	RAL 7021	Steel	Paint	Standard
21630-264	RAL 7021	Steel	Paint	Standard

Table 3/5

色号	色卡	色名	色号	色名
21630-231	RAL 7021	深蓝色	00	深蓝色
21630-273	RAL 7021	深蓝色	00	深蓝色
21630-079	RAL 7021	深蓝色	00	深蓝色
21630-272	RAL 7021	深蓝色	00	深蓝色
21630-051	RAL 7021	深蓝色	00	深蓝色
21630-477	RAL 7021	深蓝色	00	深蓝色
21630-278	RAL 7021	深蓝色	00	深蓝色
21630-232	RAL 7021	深蓝色	00	深蓝色
21630-472	RAL 7021	深蓝色	00	深蓝色
21630-271	RAL 7021	深蓝色	00	深蓝色
21630-227	RAL 7021	深蓝色	00	深蓝色
21630-233	RAL 7021	深蓝色	00	深蓝色
21630-247	RAL 7021	深蓝色	00	深蓝色
21630-284	RAL 7021	深蓝色	00	深蓝色
21630-223	RAL 7021	深蓝色	00	深蓝色
21630-082	RAL 7021	深蓝色	00	深蓝色
21630-241	RAL 7021	深蓝色	00	深蓝色
21630-045	RAL 7021	深蓝色	00	深蓝色
21630-249	RAL 7021	深蓝色	00	深蓝色
21630-468	RAL 7021	深蓝色	00	深蓝色

Table 4/5

色号	色卡	色名	色号	色名
21630-248	RAL 7021	深蓝色	00	深蓝色
21630-465	RAL 7021	深蓝色	00	深蓝色
21630-932	RAL 7021	深蓝色	00	深蓝色
21630-242	RAL 7021	深蓝色	00	深蓝色
21630-044	RAL 7021	深蓝色	00	深蓝色
21630-931	RAL 7021	深蓝色	00	深蓝色
21630-222	RAL 7021	深蓝色	00	深蓝色
21630-933	RAL 7021	深蓝色	00	深蓝色
21630-243	RAL 7021	深蓝色	00	深蓝色
21630-221	RAL 7021	深蓝色	00	深蓝色
21630-246	RAL 7021	深蓝色	00	深蓝色





?????????:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE