


# 编码条



编码安装在连接器侧面。通过编码，只有编码板才能放入正确的插槽中。

## 认证



## 功能

机械编码可防止 PSU 安装在错误的插槽上, 空间要求 4 HP

母带 (2 项) , 安装在 PSU 上

编码带 (第 1 项) 安装在 Z/水平轨道上

编码引脚 (第 3 项) 安装在编码带 (第 1 项) 上

拆除母带中适当位置的螺柱

通过 2 编码引脚, 有 66 种编码可能性

## 技术参数

搭配: 19" 电源

类型: 编码条

产品类型: 编码/键控指示器

材料: 聚对苯二甲酸丁二醇酯

Table 1/1

| 物料号 | 包装数量 | 引脚数 | 认证 |
|-----|------|-----|----|
|-----|------|-----|----|

|           |   |       |      |
|-----------|---|-------|------|
| 60800-123 | 1 | (1) 2 | RoHS |
| 60800-122 | 1 |       |      |

其他产品详情

编码带；编码块；键控带

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE