

Socket Strip, IEC, 3-Phase

Data Solutions



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 and C19 outlets with 3 phase input.

CERTIFICATIONS



FEATURES

Socket strips with IEC sockets in accordance with IEC 60320

Vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m

Mounting height 1 U

SPECIFICATIONS

- Material:** Aluminum; Polyamide
- Color:** Grey; Black; Red
- Product Type:** Socket Strip

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Package Quantity | Depth |
|----------------|-------------|-----------------|------------------|------------|------------------|-------|
|----------------|-------------|-----------------|------------------|------------|------------------|-------|

| | | | | | | |
|-----------|------------------|----|----|------|---|------|
| 60110-283 | IEC C13 | 18 | No | 400V | 1 | 44mm |
| 60110-284 | IEC C13, IEC C19 | 24 | No | 400V | 1 | 44mm |
| 60110-285 | IEC C13, IEC C19 | 30 | No | 400V | 1 | 44mm |

Table 2/2

| Catalog Number | Finish | Height | Length |
|----------------|----------|--------|---------|
| 60110-283 | Anodized | 44mm | 947.5mm |
| 60110-284 | Anodized | 44mm | 947.5mm |
| 60110-285 | Anodized | 44mm | 1753mm |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE