

# Non-Insulated Solid Conductor



## FEATURES

Solid cable for a variety of applications

Available in smaller spool sizes for convenience

LPA and LPC parts are used for lightning protection system downconductor or grounding applications

## SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Conductor Size	Cross Section	Diameter (Ø)
ASC0850	711530	Aluminum	Bare	8 mm Solid	50.3mm <sup>2</sup>	8 mm
RSCC8100	197860	Steel	Hot-Dip Galvanized	1/0 Solid	50.3mm <sup>2</sup>	8 mm
RSCC4SS850	197693	Stainless Steel 316L (EN 1.4404)	Bare	1/0 Solid	50.3mm <sup>2</sup>	8 mm
RSCC2SS830	197685	Stainless Steel 304 (EN 1.4301)	Bare	1/0 Solid	50.3mm <sup>2</sup>	8 mm
RSCC4SS830	197692	Stainless Steel 316L (EN 1.4404)	Bare	1/0 Solid	50.3mm <sup>2</sup>	8 mm
RSCC2SS850	197686	Stainless Steel 304 (EN 1.4301)	Bare	1/0 Solid	50.3mm <sup>2</sup>	8 mm
RC-ET-8	198210	Copper	Tinned	1/0 Solid	50.2mm <sup>2</sup>	8 mm

Catalog Number	Article Number	Material	Finish	Conductor Size	Cross Section	Diameter (Ø)
RC-EC-8	198160	Copper	Bare	1/0 Solid	50.2mm <sup>2</sup>	8 mm
RSCC4SS1030	197695	Stainless Steel 316L (EN 1.4404)	Bare	3/0 Solid	78.6mm <sup>2</sup>	10 mm
RSCC4SS1050	197696	Stainless Steel 316L (EN 1.4404)	Bare	3/0 Solid	78.6mm <sup>2</sup>	10 mm

Table 2/2


Catalog Number	Article Number	Length (L)	Unit Weight	Complies With
ASC0850	711530	50m	0.14 kg	
RSCC8100	197860	125m	0.4 kg	
RSCC4SS850	197693	50m	0.4 kg	
RSCC2SS830	197685	30m	0.4 kg	
RSCC4SS830	197692	30m	0.4 kg	
RSCC2SS850	197686	50m	0.4 kg	
RC-ET-8	198210	100m	0.45 kg	
RC-EC-8	198160	100m	0.45 kg	IEC® EN 62561-2
RSCC4SS1030	197695	30m	0.63 kg	
RSCC4SS1050	197696	50m	0.63 kg	

## ADDITIONAL PRODUCT DETAILS

Unit weight is per foot (0.3048 m).

Cut-to-order (CTO) lengths are available for an additional charge.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**