

Rail Crown Socket



FEATURES

- Cast bronze mechanical electrical connection to rail
- Crown socket is tin plated to improve rail interface electrical properties
- Primarily for traction power negative return current
- Secured to the rail with a threaded tapered pin
- Attaches to cable simply and permanently using the nVent ERICO Cadweld connection process
- Suitable for cables up to and including 500 kcmil/240 mm²
- Available for field-made applications or as part of a factory-made assembly
- No special tools required

SPECIFICATIONS

Table 1/1		
Catalog Number	Product	Conductor Size
B1883QA	Socket	500 kcmil Stranded, 240 mm ² Stranded
B1883QB	Pin	
B1883QC	Pin, Oversized	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE