

Horizontal E-Bend Section 90-Degree (cULus), fits 24.00, Black, Steel

Data Solutions

CATALOG NUMBER

L90HB24BLK



The 90-Degree Horizontal E-Bend Section provides a 90-degree horizontal change in cable runway direction. It is made of 1-1/2 in. x 3/8 in. (38 mm x 8 mm) tubular steel. The E-Bend connects to straight sections with butt-splice kits. It is designed for category 5e, 6, 6A and fiber optic cable.

FEATURES

The 90-Degree Horizontal E-Bend Section provides a 90-degree horizontal change in cable runway direction

It is made of 1-1/2 in. x 3/8 in. (38 mm x 8 mm) tubular steel

The E-Bend connects to straight sections with butt-splice kits

It is designed for category 5e, 6, 6A and fiber optic cable

PRODUCT ATTRIBUTES

Article Number: 17338

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 1.52mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE