

Modular Chassis, AC



DIN-rail components can be mounted quickly and easily to this chassis, both at the panel builders and in the field.

FEATURES

Description: Used for easy mounting of DIN-rail components with a maximum height of 68 mm. Distance between rows 125 mm. If required, the standard enclosure door can be replaced with a glazed door. Usable depth between front cover and external door: 35 mm. In stainless steel enclosure machining is required.

Material: DIN-rails PP0735 made of 1.2 mm galvanized steel, vertical profiles 1.5 mm mild steel, and front cover 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: Slotted front panel, two vertical profiles, top and bottom blank panels, one DIN-rail per row, and mounting accessories.

Mounting requirements: To be assembled on MAS and ASR enclosures.

SPECIFICATIONS

Thickness:	1.2mm
Color:	Light Gray
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 7035

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Module Quantity
AC04030R5		400mm	300mm	98mm	Mild Steel	33
AC10060R5	1202358	1000mm	600mm	98mm	Mild Steel	189
AC07050R5		700mm	500mm	98mm	Mild Steel	110
AC05040R5		500mm	400mm	98mm	Mild Steel	48
AC06060R5		600mm	600mm	98mm	Mild Steel	108
AC08060R5		800mm	600mm	98mm	Mild Steel	162
AC10080R5	1202359	1000mm	800mm	98mm	Mild Steel	266
AC06040R5		600mm	400mm	98mm	Mild Steel	64
AC03025R5		300mm	250mm	98mm	Mild Steel	16

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE