Compression Straight Lug, Heavy-Duty DIN46235, 1/0 Stranded, 50 mm² Stranded, 10.5 mm Hole

Data Solutions

CATALOG NUMBER

PKS5010H

FEATURES

- Tin plated for corrosion prevention
- Annealed copper eases the crimping operation
- Optimized sizes to the most efficient electrical conductivity
- Best mechanical behavior (vibration/pull-out); DIN EN 61373 Class 1B “Railway Applications"
- Markings on barrel for crimping
- Consistent material thickness, precise diameter and accurate cable fit; DIN46235

PRODUCT ATTRIBUTES

- Article Number: 715113
- Material: Copper
- Finish: Tinned
- Lug/Connector Type: Heavy-Duty DIN46235
- Conductor Size: 1/0 Stranded; 50 mm² Stranded
- Hole Size (HS): 10.5mm

Length (L): 65mm

Width (W): 21mm

Tool/Die Type: M2M or M2H/PKM2; M3H or M3B/PKM3; MLB/PKML

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.