

Front Panel, U-profile, Retrofit Shielding



U-profile front panel for textile EMC gasket.

CERTIFICATIONS



FEATURES

U-profile, front panel, Al, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPECIFICATIONS

| | |
|------------------------|----------------------------|
| Depth (D): | 2.5mm |
| Material: | Aluminum |
| Finish: | Anodized; Passivated |
| Accessory Type: | Front panel |
| Product Type: | Front Panel |
| Type: | Front Panel without Handle |
| EMC Shielding: | No (Retrofittable) |

Table 1/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------|-------------|--------------|
|----------------|-------------|------------|------------------|----------|-------------|--------------|

| | | | | | | |
|-----------|----|------|---|----------------|-------------|----------|
| 30848-385 | 3U | 9HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-354 | 3U | 4HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-120 | 6U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-387 | 6U | 10HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-047 | 3U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-139 | 6U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-650 | 5U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-381 | 6U | 6HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-386 | 3U | 10HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-160 | 6U | 63HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-649 | 5U | 63HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-269 | 4U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-380 | 3U | 6HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-206 | 2U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-382 | 3U | 7HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-270 | 4U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-648 | 5U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-262 | 2U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-027 | 3U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-384 | 3U | 9HP | 1 | Screw-on Front | Textile EMC | Anodized |

Table 2/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------------|-------------|--------------|
| 20848-647 | 5U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-268 | 4U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-383 | 6U | 7HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-280 | 9U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-357 | 6U | 8HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-068 | 3U | 63HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-260 | 2U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-013 | 3U | 14HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-359 | 6U | 12HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30849-005 | 6U | 3HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-189 | 6U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-015 | 3U | 16HP | 1 | Screw-on Front | Textile EMC | Anodized |

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------------|-------------|--------------|
| 30848-378 | 3U | 5HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-020 | 3U | 21HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30849-004 | 3U | 3HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-358 | 3U | 12HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-106 | 6U | 14HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-379 | 6U | 5HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-108 | 6U | 16HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30849-002 | 6U | 2HP | 1 | Screw-on Front | Textile EMC | Anodized |

Table 3/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------------|-------------|--------------|
| 30848-356 | 3U | 8HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-097 | 3U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-271 | 4U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-355 | 6U | 4HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-113 | 6U | 21HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-261 | 2U | 63HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30849-001 | 3U | 2HP | 1 | Screw-on Front | Textile EMC | Anodized |

Table 1/3

| Catalog Number | Rear Finish | Treated Edges | Complies With | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-385 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 45.38mm | |
| 30848-354 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 20mm | RoHS |
| 20848-120 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 141.9mm | RoHS |
| 30848-387 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 50.5mm | RoHS |
| 20848-047 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 213mm | RoHS |

| Catalog Number | Rear Finish | Treated Edges | Complies With | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 20848-139 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 213mm | RoHS |
| 20848-650 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm | 426.4mm | |
| 30848-381 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 30.1mm | RoHS |
| 30848-386 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 50.5mm | RoHS |
| 20848-160 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 319.7mm | RoHS |
| 20848-649 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm | 319.7mm | |
| 20848-269 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm | 213mm | RoHS |
| 30848-380 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 30.1mm | RoHS |
| 20848-206 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 84mm | 141.9mm | |
| 30848-382 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 35.2mm | RoHS |
| 20848-270 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm | 213mm | RoHS |
| 20848-648 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm | 213mm | |
| 20848-262 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 84mm | 426.4mm | RoHS |
| 20848-027 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 141.9mm | RoHS |

| Catalog Number | Rear Finish | Treated Edges | Complies With | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-384 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 45.38mm | |

Table 2/3

| Catalog Number | Rear Finish | Treated Edges | Complies With | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 20848-647 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm | 141.9mm | |
| 20848-268 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm | 141.9mm | RoHS |
| 30848-383 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 35.2mm | RoHS |
| 20848-280 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 395.1mm | 426.4mm | RoHS |
| 30848-357 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 40.3mm | RoHS |
| 20848-068 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 319.7mm | RoHS |
| 20848-260 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 84mm | 213mm | |
| 20848-013 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 70.8mm | RoHS |
| 30848-359 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 60.6mm | RoHS |
| 30849-005 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 14.9mm | |
| 20848-189 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 426.4mm | RoHS |
| 20848-015 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 80.9mm | RoHS |

| Catalog Number | Rear Finish | Treated Edges | Complies With | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-378 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 25mm | RoHS |
| 20848-020 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 106.3mm | RoHS |
| 30849-004 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 14.9mm | RoHS |
| 30848-358 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 60.6mm | RoHS |
| 20848-106 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 70.8mm | RoHS |
| 30848-379 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 25mm | RoHS |
| 20848-108 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 80.9mm | RoHS |
| 30849-002 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 9.8mm | RoHS |

Table 3/3

| Catalog Number | Rear Finish | Treated Edges | Complies With | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-356 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 40.3mm | RoHS |
| 20848-097 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm | 426.4mm | RoHS |
| 20848-271 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm | 426.4mm | RoHS |
| 30848-355 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 20mm | RoHS |
| 20848-113 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm | 106.3mm | RoHS |

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE