

FleXbus IP55 Conductor Entry, Double Entry, 6.929" x 6.181" x 5.984"

Data Solutions

CATALOG NUMBER

FLEXCEIP55C1002



nVent ERIFLEX FleXbus IP55 Conductor Entries can be used for switchboard and/or power supply cover to upgrade an installation to IP55 level. Protect the nVent ERIFLEX FleXbus Conductor insulation against sharp edges from power supply or switchboard top cover.

CERTIFICATIONS



FEATURES

Made with soft PVC to follow any potential conductor bending radius

Sealing around the conductor is made by a self-fusing tape with a strong adhesive

Good resistance to solvent and hydrocarbon splashes

Adaptable to any nVent ERIFLEX FleXbus conductor cross section by cutting the top material with traditional cutter

High acid resistance

UV resistance


RoHS compliant

Flame retardant

PRODUCT ATTRIBUTES

Article Number: 508143
Material: Polyvinylchloride
Enclosure Rating: IP 55
Type: Double Entry
Working Temperature: -40 to 284°F
A: 6.93in
B: 6.18in
C: 5.98in
Conductor Size: 960 mm²; 1280 mm²; 1810 mm²
Torque (TQ): 1.84ft·lbf
Unit Weight: 2.2lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE