

DT Panel Protector, 120 kA, Filter, 480 V, 3PhΔ 3W+G Dist System

Data Solutions

CATALOG NUMBER

DTX120F480D



The nVent ERICO DTX120 Series of Surge Protective Devices (SPD) features North American and Worldwide standards compliance and provides premium protection against damaging transients and surge currents, particularly in IEC Class I & Class II and UL Type 1 & Type 2 locations. The innovative design allows for installation on the line or load of the service panels and removes the need for circuit breakers (B Version Only). With a 120 kA per phase surge rating, DTX120 is well suited for category C locations. It is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX120 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

CERTIFICATIONS



FEATURES

Excellent clamping and low UL voltage protection ratings

Features relay alarming for power/phase loss and status of SPD health

Design allows for easy removal and replacement of surge modules via lever assist

RS-485 Interface Standard

Up to 53 dB attenuation (10 kHz to 100 MHz)

10 Year Warranty

PRODUCT ATTRIBUTES

Nominal System Voltage (Un): 480 V

Distribution System: 3PhΔ 3W+G

Max Continuous Operating Voltage (Uc): 510 VAC

Max Discharge Current (Imax), Per Phase: 120kA 8/20 μs

Impulse Current (Iimp), Per Mode: 12.5kA 10/350 μs

Filtering: -29 dB @ 100 kHz

Frequency: 50 – 60Hz

Voltage Protection Rating (VPR), L-G: 1800V

Voltage Protection Rating (VPR), L-L: 1800V

Protection Modes: L-PE

Short Circuit Current Rating (SCCR): 200kA

Nominal Discharge Current (In), IEC: 40kA 8/20 μs

Nominal Discharge Current (In), UL: 20kA 8/20 μs

Voltage Protection Level (Up), IEC: 1200 V @ 20 kA; 3000 V @ 100 kA

Short Circuit Current Rating (Iscrr): 50kA

Temperature: -40 to 176°F

Enclosure Material: Metal with PC Lid

Enclosure Rating: NEMA®-4X; UL® 50E Type 4

Lead Size imperial: #14 - #6

Mounting: 4 Screw Locations

Remote Contact Switching Capacity: 2.0 A @ 240 V

Remote Contacts: Yes (Form C)

Status Indication: Audible alarm with silence switch; Dual color status LED; Mechanical flag; OLED Display; Surge/TOV Counter, Resettable

Technology: Hybrid technology utilizing thermal disconnects

Certification Details: CSA C22.2 No. 269.2; UL® 1283 Edition 7; UL® 1449 Edition 5 Type 2, 20 kA Mode

Complies With: ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C; ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C; ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C; EN 61643-11 Type 2; IEC® 61643-11 Class II

Depth (D): 3.87in

Height (H): 13.02in

Width (W): 4in

Unit Weight: 6.35lb

Replacement Module: DT2510DTXM

ADDITIONAL PRODUCT DETAILS

Optional Flush Plate and Side Mount Kits available: DTX120FP & DTX120SM

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE