


MPO PDU, 0U, 60A(48A), 208V, 3P Delta, 6 CB, (21)C13, (21)4-in-1

Data Solutions

RÉFÉRENCE CATALOGUE

EN5952



The Advantage Series Outlet Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

FONCTIONS

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information

UL 2900-1 certified for safety software cybersecurity for network-connectable products

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs. Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

ATTRIBUTS DU PRODUIT

Famille de produits: Enlogic

Type: PDU intelligent

Type de produit: Bâti de prises

Type de prise: (21) C13/C15; (21) C13/C15/C19/C21

Nombre de prises: 42

Couleur: Noir

Sorties commutées: Non

Longueur de câble: 1800mm

Disjoncteur: 20 A, 2 pôles, Hy-MagA

Puissance nominale: 17.3 kVA

Nombre de disjoncteurs: 6

Valeur nominale d'interruption: 5kAIC

Tension d'entrée: 208V

Phase: Triphasé Delta

Puissance de sortie nominale: 208VAC

Tension nominale: 208V

Nombre de tensions de sortie: 42

Nombre de phases: 3

Interrupteur marche/arrêt inclus: Non

Intensité (ampérage détaré): 60 A (48 A)

Tension de sortie: 208VAC

Unités de rack: 0U

Type de prise: CEI 60309 460P9 (IP44)

Type de mesure: Sortie

Câble d'entrée amovible: Non

Matériau: Acier

Finition: Revêtement poudré

Hauteur: 1780mm

Largeur: 56mm

Profondeur: 75mm

Quantité par colis: 1

Longueur du câble d'entrée: 1.8m

INFORMATIONS COMPLÉMENTAIRES

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre portefeuille puissant de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE