

MI PDU, 0U, 100A(80A)NA/100A Int, 380-415V, 3P Wye, 18 CB, (18)C13, (18)4-in-1

Data Solutions

NÚMERO DE CATÁLOGO

EN19HD

The Advantage Series Input Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

CARACTERISTICAS

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

UL 2900-1 certified for safety software cybersecurity for network-connectable products.

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs

Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

CARACTERÍSTICAS DO PRODUTO

Família de produtos: Enlogic

Tipo: Intelligent PDU

Product Type: Socket Strip

Tipo de soquete: (18) C13/C15; (18) C13/C15/C19/C21

Socket Quantity: 36

Cor: Black

Switched Outlets: Não

Comprimento do cabo: 1800mm

Power Rating: 57.6 kVA North America; 69 kVA International

Circuit Breaker: 20 A, 1-pole, Hy-MagA

Circuit Breaker Quantity: 18

Nominal Power Output: 230VAC

Tensão nominal: 415V

Number of Output Voltages: 36

On/Off Switch Included: Não

Output Voltage: 208 – 230VAC

Amperage (Derated Amperage): 100 A (80 A) North America; 100 A International

Plug Type: IEC 60309 5125P6W (IP67)

Rack Units: 0U

Removable Input Cable: Não

Metering Type: Input

Material: Aço

Acabamento: Pintura electrostática com Acabamento Texturado

Altura: 1750mm

Largura: 59mm

Profundidade: 87mm

Quantidade por embalagem: 1

Input Cable Length: 1.8m

DETALHES ADICIONAIS DO PRODUTO

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha

qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE