We connect and protect

Basic PDU, EB0450, 400 VAC, 3-PH, 16 A

Data Solutions

NÚMERO DE CATÁLOGO

EB0450

Modular, compact PDU. Ultra-Low Profile Design

CARACTERISTICAS

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

CARATERÍSTICAS DO PRODUTO

Família de produtos: Enlogic

Tipo: Basic PDU

Product Type: Socket Strip

Tipo de soquete: (21) C13/C19

Socket Quantity: 42

Cor: Black

Circuit Breaker: No Circuit Breaker

Switched Outlets: Não

Circuit Breaker Quantity: 0

Power Rating: 11.5 kVA North America; 11.0 kVA International

Input Cable Length: 1.8m

Input Cable Location: Top Feed

Input Voltage: 380 – 415V

Phase: 3 PH

Tensão nominal: 415V

Max Power Input: 11.5 / 11.0 kVA

On/Off Switch Included: Não

Amperage (Derated Amperage): 20 A (16 A) North America; 16 A International

Output Voltage: 208 – 230VAC

Rack Units: 0U

Plug Type: IEC 60309 520P6/516P6

Metering Type: None

Removable Input Cable: Não

Material: Aço

Acabamento: Pintura electrostática com Acabamento Texturado

Altura: 1490mm

Largura: 56mm

Profundidade: 55mm

Peso: 9.5kg

Quantidade por embalagem: 1

DETALHES ADICIONAIS DO PRODUTO

Please order bracket for vertical mounting separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.